

to determine when your case will be delivered, simply choose the pickup day across the top, and trace down to the row of the product you are ordering

	Day of pick up:	Days	Mon	Tue	Wed	Thur	Fri	
Fixed	FCZ: Full Contour Zirconia EZ: Esthetic Zirconia Emax Monolithic	7	Next Tue	Next Wed	Next Thur	Next Fri	Mon after next	
	Emax Layered FCC:Full Cast Crown PFZ:Porcelain Fused to Zirconia	9	Next Thur	Next Fri	Mon after next	Tue after next	Wed after next	
	PFM: Porcelain Fused to Metal	10	Next Fri	Mon after next	Tue after next	Wed after next	Thur after next	
Removables	Reline/Simple Repair* Flipper (1-2 teeth) Custom Tray, Wax Rim	5	This Fri	Next Mon	Next Tue	Next Wed	Next Thur	
	Denture Set Up Denture Finish Hard/Soft nightguard Hard Night guard Immediate Denture	7	Next Tue	Next Wed	Next Thur	Next Fri	Mon after next	
	Cast Partial Framework	12	12 business days					
	Flexible Processing	14	14 business days					
Call for details	Need it RUSHED?		We know that sometimes you may need a case even faster than our standard turnaround, so we offer Rush Cases at no charge. All we ask is a little heads up. Just give us a call with the details and we'll do everything possible to accommodate you.					
	*Same Day/Next Day Repairs & Relines		We offer same and next day simple repairs and rellines for office within a certain radius of the lab. Please call for details.					
	Crown Fit to Partial	We understand that patients do not want to be without their partial while we fabricate their crown, so we have several options to help you balance the need for accuracy with your patient's comfort. Sev- eral variables can impact the turnaround for these cases, so please call to discuss the particulars.						



TURNAROUND REFERENCE

Titanium and Zirconia Implant Abutments

to determine when your case will be delivered, simply choose the pickup day across the top, and trace down to the row of the product you are ordering

DL Custom Abutment with FCZ Crown DL Custom Abutment with EZ Crown								
DL Screw Retained with PFZ Crown	10	Next Fri	Mon after next	Tue after next	Wed after next	Thur after next		
DL Screw Retained FCZ DL Screw Retained EZ	8	Next Wed	Next Thur	Next Fri	Mon after next	Tue after next		
DL Custom Abutment with PFZ Crown	11	Mon after next	Tue after next	Wed after next	Thur after next	Fri after next		
lantis Custom Abutment lantis Screw Retained mmer Biomet Custom Abutment mmer Biomet Encode Abutment	12	12 business days						
ohorizons Custom Abutment obelProcera Custom Abutment raumann Custom Abutment	14	14 business days						
bbel ASC Screw Retained FCZ	12	12 business days						
bbel ASC Screw Retained PFZ	14	14 business days						
	L Screw Retained EZ L Custom Abutment with PFZ Crown antis Custom Abutment antis Screw Retained mer Biomet Custom Abutment mer Biomet Encode Abutment horizons Custom Abutment pelProcera Custom Abutment aumann Custom Abutment pel ASC Screw Retained FCZ	Screw Retained EZ8L Custom Abutment with PFZ Crown11antis Custom Abutment antis Screw Retained mer Biomet Custom Abutment horizons Custom Abutment belProcera Custom Abutment aumann Custom Abutment121212aumann Custom Abutment bel ASC Screw Retained FCZ12	&Next WedL Screw Retained EZ8Next WedL Custom Abutment with PFZ Crown11Mon after nextantis Custom Abutment1212amer Biomet Custom Abutment1212horizons Custom Abutment1414belProcera Custom Abutment14aumann Custom Abutment12	L Screw Retained EZ8Next WedNext ThurL Custom Abutment with PFZ Crown11Mon after nextTue after nextantis Custom Abutment antis Screw Retained mer Biomet Custom Abutment horizons Custom Abutment belProcera Custom Abutment1212121214aumann Custom Abutment bel ASC Screw Retained FCZ12	Screw Retained EZ8Next WedNext ThurNext FriL Custom Abutment with PFZ Crown11Mon after nextTue after nextWed after nextantis Custom Abutment antis Screw Retained mer Biomet Custom Abutment horizons Custom Abutment belProcera Custom Abutment121212 business daysbel ASC Screw Retained FCZ121212 business days	L Screw Retained EZ8Next WedNext ThurNext FriMon after nextL Custom Abutment with PFZ Crown11Mon after nextTue after nextWed after nextThur after nextantis Custom Abutment antis Screw Retained mer Biomet Custom Abutment horizons Custom Abutment 		

In our continuous drive to provide the greatest customer experience, Artisan Dental Laboratory implemented latest CAD/CAM technologies such as 3D Scanning, 5-axis milling, and 3D printing all processed in our lab. We perform weekly calibrations and daily maintenance to make sure our products are accurate and consistent. On top of that, two of our master technicians with more than 50 years combined experience oversee each cases. Any complex cases can be solved by our latest technology implmentation and experience. This assures Artisan dental lab's clients that they are receiving highest quality results with fast turn around time.

We want to have complete information on all implant cases. Please include Brand, size, platform, and product numbers of all components used identified by tooth number position.

Vew in 2019